
Sample pulverizer



Application

Lab/Laboratory Sample pulverizer is suitable for crushing all kinds of hard metallic or nonmetallic ores and mineral raw materials, and it can be used by geological, metallurgical, coal, building materials, petroleum, chemical industry, scientific research and experiment departments and units that need to crush test samples.

Sample pulverizer machine is working, the motor drives the rotating shaft of the power arm to rotate, and under the action of centrifugal force, a large vibration is generated to make the vibration of the parameters regular, and at the same time, the striking ring and hitting block are forced to strike, squeeze and grind the samples of the bowl in the bowl, so as to achieve the purpose of crushing.

Main technical parameters

model	Bowl material	Bowl quantity (pcs)	Capacity (g)	Feeding size (mm)	Output size (mesh)	Mill time (min)	weight (kg)	motor (kw)	dimension (mm)		
									L	W	H
GJ-A	Steel jade	1	30	< 5	200-400	10~30	80	0.55	500	490	680
GJ-B	Steel jade	3	30	< 5	200-400	10~30	100	1.1	530	530	800
1MZ-100	High manganese steel	1	100	< 12	120~200	3~5	145	1.1	560	560	800
2MZ-100	High manganese steel	2	2*100	< 12	120~200	3~5	180	1.1	560	560	800
3MZ-100	High manganese steel	3	3*100	< 12	120~200	3~5	180	1.1	560	560	800
4MZ-100	High manganese steel	4	4*100	< 12	120~200	10~15	330	1.5	740	740	910
5MZ-100	High manganese steel	5	5*100	< 12	120~200	10~15	330	1.5	740	740	910
6MZ-100	High manganese steel	6	6*100	< 12	120~200	3~5	330	1.5	740	740	910
1MZ-200	High manganese	1	1*200	< 15	120~200	3~5	180	1.1	560	560	800

	steel										
2MZ-200	High man gane se steel	2	2*2 00	< 15	120~200	3~5	310	1.5	740	740	850
3MZ-200	High man gane se steel	3	3*2 00	< 15	120~200	3~5	310	1.5	740	740	850
4MZ-200	High man gane se steel	4	4*2 00	< 15	120~200	3~5	310	1.5	740	740	850
2MZ-400	High man gane se steel	2	2*4 00	< 15	120~200	3~5	310	1.5	740	740	850
3MZ-400	High man gane se steel	3	3*4 00	< 15	120~200	3~5	310	1.5	740	740	850
1MZ1000	High man gane se steel	1	1*1 000 g	< 12	120~200	3~5	330	1.1	740	740	910



7mz-100 Sample pulverizer



6MZ-100 Sample pulverizer



5MZ-100 Sample pulverizer



4MZ-100 Sample pulverizer



3MZ-100 Sample pulverizer



2MZ-100 Sample pulverizer



WELL-TECH EQUIPMENT
威尔国际矿业装备

1MZ-100 Sample pulverizer